



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue



By Bryant
Catalog # 26520

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black phenolic with long aluminum housing and lift cover

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel screws provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	26520
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Style	Grounding
Type	Receptacle
UPC	781786574205

Dimensions

Dimensions	4.62 in x 3.50 in x 3.57 in
Display Size	Standard Sized Product
Height	3.57 in
Length	4.62 in
Width	3.5 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current Rating	60 A
Phase	Multi Phase
Voltage Rating	600 VAC
Voltage Rating Description	600V AC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 26520 Specification Sheet French](#)
- [Specifications - 26520 Specification Sheet English](#)