



Straight Blade Devices, Specialty Receptacles, Clock Hanger, Receptacle and Plate, 15A 125V, 5-15R, Smooth Brushed Brass Plate

By Bryant
Catalog # 2828G

Straight Blade Devices, Specialty Receptacles, Clock Hanger, Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Smooth Brushed Brass Plate, Single Pack

Features

- Clock Hanger
- Receptacle and Plate
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Commercial/Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875

Voltage Rating	125 V
----------------	-------

Dimensions

Display Size	Standard Sized Product
Length	4.63 in
Width	2.88 in
Weight	0.45 lb.
Height	2.10 in
Dimensions	4.63 in x 2.88 in x 2.10 in

General

Series	Special Use
OEM Brand Name	Hubbell Bryant
Style	Clock Hanger / Recessed Receptacles
Color	Brass
Item Type	Clock Hanger Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786619012

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)