



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Short Toggle

By Bryant
Catalog # 30002DS

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Short Toggle, Black

Features

- Toggle
- Motor Disconnects
- Double Pole
- 30A 600V AC
- Back and Side Wired

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Poles	2 Pole
-----------------	--------

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	18000
Voltage Rating	600V AC kV

Dimensions



Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Series	Short Toggle
OEM Brand Name	Hubbell Bryant
Style	Motor Controller/Disconnect
Item Type	Open Switch
Material - Mounting Hardware	Screw Mounting
Type	Back & Side Wire
UPC	781786631519

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

- Catalog [\[English\]](#)
- Catalog Page [\[English\]](#)
- Catalog Page [\[English\]](#)
- Catalog Page [\[English\]](#)