



## Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Black

By Bryant  
Catalog # 30003D



\*Representative Image

Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side  
Wired Only, Black

### Features

- Toggle
- Motor Disconnects
- Three Pole
- 30A 600V AC
- Side Wired Only

### General

Catalog Number	30003D
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back & Side Wire
UPC	781786631533

### Dimensions

Display Size

Standard Sized Product

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

### Certifications And Compliance

Standards - RoHS Compliance Status	CM
---------------------------------------	----

### Logistics

Carton Quantity	10
Pallet Quantity	2640

### Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 30003D Specification Sheet French](#)  
[Specifications - 30003D Specification Sheet English](#)



A Hubbell brand