



Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Aluminum, With NEMA 1 Enclosure

By Bryant
Catalog # 30103D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Aluminum, With NEMA 1 Enclosure

Features

- Toggle
- Motor Disconnects
- Three Pole
- 30A 600V AC
- Side Wired Only

Application

Standard Toggle

Specifications

Environmental Conditions	Indoor Only
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

Conductor

Number Of Poles	3 Pole
-----------------	--------

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Three Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	18000
Voltage Rating	600V AC kV



Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Enclosure Type	NEMA 1
Series	Non-Fused
OEM Brand Name	Hubbell Bryant
Style	Standard Duty
Item Type	Enclosed Switch
Material - Mounting Hardware	Screw Mounting
Type	Disconnect Switches
UPC	781786631564

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)