



Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant
Catalog # 30302D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Side Wired Only, Black, With NEMA 3R Enclosure

Features

- Toggle
- Motor Disconnects
- Double Pole
- 30A 600V AC
- Side Wired Only

Application

Red Slide

Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

Conductor

Number Of Poles	2 Pole
-----------------	--------

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	18000



Voltage Rating	600V AC kV
----------------	------------

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Enclosure Type	NEMA 3R
Series	Non-Fused
Style	Standard Duty
Item Type	Enclosed Switch
Material - Mounting Hardware Type	Screw Mounting Disconnect Switches
UPC	781786631571

Logistics

Carton Quantity	4
-----------------	---

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

[Catalog \[English\]](#)