



Disconnect Switches, 3-Pole, 30A 600V AC, In NEMA 3R Flip Lid Enclosure

By Bryant
Catalog # 30313D

Disconnect Switches, 3-Pole, 30A 600V AC, In NEMA 3R Flip Lid Enclosure



Features

- 30A 600V AC
- In NEMA 3R Flip Lid Enclosure

Application

Lift Cover

Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No

Conductor

Number Of Poles	3 Pole
-----------------	--------

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Three Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	18000
Voltage Rating	600V AC kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Enclosure Type	NEMA 3/3R
Series	Non-Fused
OEM Brand Name	Hubbell Bryant
Style	Standard Duty
Item Type	Enclosed Switch
Material - Mounting Hardware	Screw Mounting
Type	Disconnect Switches
UPC	781786631601

Logistics

Carton Quantity	4
-----------------	---

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)