



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, NEMA 3R Box and Switch

By Bryant
Catalog # 30323D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Black, NEMA 3R Box and Switch

Features

- Toggle
- Motor Disconnects
- Three Pole
- 30A 600V AC
- Side Wired Only

Application

Red Handle

General

Catalog Number	30323D
EU RoHS Indicator	No
Enclosure Type	NEMA 3/3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty

Type Disconnect Switches
UPC 781786631625

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
Pallet Quantity	480

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 30323D Specification Sheet English](#)
- [Specifications - 30323D Specification Sheet French](#)