



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 30A 250V, 2-
Pole 3-Wire Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 3330

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Only
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A



Voltage Rating Description	125/250V AC
Phase	Multi Phase
Connectivity	Terminal Screws
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.71 in
Height	1.20 in
Dimensions	3.28 in x 1.71 in x 1.20 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Plug-In
Type	Receptacle
Material	Nylon
UPC	781786619685

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)