



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 30A 250V, 2-
Pole 3-Wire Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 3330G

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
30A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Flush Receptacle
- 30A 250V
- 2-Pole 3-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	250V AC



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle- For Replacement Use
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786619692

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)