



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 30A 3-Phase
Wye 120/208V AC, 4-Pole 4-Wire Non-
Grounding, Non-NEMA, Screw Terminal

By Bryant
Catalog # 3430BRY

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non- Grounding,
Non-NEMA, Screw Terminal, Black

Features

- Flush Receptacle
- 30A 3-Phase Wye 120/208V AC
- 4-Pole 4-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A



Voltage Rating Description	3 Phase Y 120/208V AC
Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786619906

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)



A Hubbell brand