



Locking Devices, Locking Devices,
Industrial, Male Plug, 20A 3-Phase Wye
120/208V AC, 4-Pole 5-Wire Grounding,
Non- NEMA, Screw Terminal and White

By Bryant
Catalog # 3521

Locking Devices, Locking Devices, Industrial, Male Plug, 20A 3-
Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Non- NEMA,
Screw Terminal, Black and White

Features

- Industrial
- Male Nylon Plug
- 20A 3-Phase Wye 120/208V AC
- 4-Pole 5-Wire Grounding
- Non- NEMA

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	3 Phase Y 120/208 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized
Length	2.11 in
Width	2.11 in
Height	2.60 in
Dimensions	2.11 in x 2.11 in x 2.60 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Nylon Plug-For Replacement Use
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786620049

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)