



Lampholders, Medium Base, Prefocus Incandescent Lampholder, 500W 250V

By Bryant
Catalog # [3743R](#)

Lampholders, Medium Base, Prefocus Incandescent Lampholder,
500W 250V

Features

- Prefocus Incandescent Lampholder
- 500W 250V

Specifications

EU RoHS Indicator No

Configuration

Base Type Surface or Clamp Mount

Current

Amperage Rating 4 A
Frequency Rating 60 Hz
Connectivity Screw Terminals
Voltage Rating 250V AC kV



Dimensions

Lamp Size Prefocus Bayonet

General

OEM Brand Name Hubbell Bryant
Color Black
Material - Mounting Hardware Screw Mounting
Material Composite
UPC 781786200968

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)