



## Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 40A, 600V AC, Side Wired Only, Black

By Bryant  
Catalog # 40003D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 40A, 600V AC, Side Wired Only, Black



### Features

- Toggle
- Motor Disconnects
- Three Pole
- 40A
- 600V AC

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

### Conductor

Number Of Poles	3 Pole
-----------------	--------

### Current

Current Rating	40 A
Amperage Rating	40 A
Voltage Rating Description	600V AC kV
Phase	Three Phase
Current / Amperage Rating	40 A
Connectivity	Pressure Terminal Screws
Wattage	24000
Voltage Rating	600V AC kV

### Dimensions

Display Size Standard Sized Product

### Force Related

Load Capacity Inductive

### General

Series	Standard Toggle
OEM Brand Name	Hubbell Bryant
Style	Motor Controller/Disconnect
Item Type	Open Switch
Material - Mounting Hardware	Screw Mounting
Type	Side Wire
UPC	781786631656

### Logistics

Carton Quantity 10

### Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)