



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 40A 120/277V AC, Side Wired Only, Brown

By Bryant
Catalog # 4002

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 40A 120/277V AC, Side Wired Only, Brown

Features

- Toggle
- Manual Motor Controllers
- Double Pole
- 40A 120/277V AC
- Side Wired Only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Number Of Poles	2 Pole
-----------------	--------

Current

Current Rating	40 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	24000
Voltage Rating	600V AC kV



Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Series	Standard Toggle
OEM Brand Name	Hubbell Bryant
Style	Motor Controller Only
Item Type	Open Switch
Material - Mounting Hardware	Screw Mounting
Type	Side Wire
UPC	781786925335

Logistics

Carton Quantity	10
Pallet Quantity	5400

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)