



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 20A 3-Phase
Wye 120/208V AC 400Hz, 4-Pole 5-Wire
Grounding, Non-NEMA, Screw Terminal

By Bryant
Catalog # 40045FR

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
20A 3-Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire
Grounding, Non-NEMA, Screw Terminal, Black

Features

- Flush Nylon Receptacle
- 20A 3-Phase Wye 120/208V AC 400Hz
- 4-Pole 5-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	20 Amp 400Hz
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 120/208V AC



Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	20A Single Urea Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786684522

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)