



Locking Devices, Locking Devices,
Industrial, Female Connector Body, 20A 3-
Phase Wye 120/208V AC 400Hz, Non-
NEMA

By Bryant
Catalog # 40045NC

Locking Devices, Locking Devices, Industrial, Female Connector
Body, 20A 3-Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire
Grounding, Non-NEMA,Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Non-Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	20 Amp 400Hz
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 120/208 VAC
Connectivity	Screw Terminals

Voltage Rating	3 Phase Y 120/208 VAC
----------------	-----------------------

Dimensions

Display Size	Standard Sized Product
Length	2.13 in
Height	3.90 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786684584

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)