



Locking Devices, Locking Devices,
Industrial, Male Plug, 20A 3-Phase Wye
120/208V AC 400Hz, Non-NEMA, 400Hz
Version

By Bryant
Catalog # 40045NP

Locking Devices, Locking Devices, Industrial, Male Plug, 20A 3-
Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire Grounding, Non-
NEMA, Screw Terminal, Black and White, 400Hz Version

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp 400Hz
Description	



Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 120/208 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786684607

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)