



Locking Devices, Locking Devices,
Industrial, Duplex Receptacle, 15A 125V, 2-
Pole 3-Wire Grounding, L5-15R, Screw
Terminal, Brown

By Bryant
Catalog # 4700DR



Locking Devices, Locking Devices, Industrial, Duplex Receptacle,
15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal,
Brown

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A

Voltage Rating Description	125V
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	0.93 in
Dimensions	3.28 in x 1.70 in x 0.93 in

General

OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Item Type	15A Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786002005

Logistics

Carton Quantity	10
Pallet Quantity	2340

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)