



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 15A 125V, 2-
Pole 3-Wire Grounding, L5-15R, Screw
Terminal, Black

By Bryant
Catalog # [4710](#)

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125V



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.41 in
Height	1.01 in
Dimensions	3.28 in x 1.41 in x 1.01 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	15A Nylon Single Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786174016

Logistics

Carton Quantity	10
Pallet Quantity	4800

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)