



# Locking Devices, Locking Devices, Marine Grade, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Yellow

By Bryant  
Catalog # 4710CR



Locking Devices, Marine Grade, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Corrosion-Resistant, Yellow

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	4710CR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786656130

## Dimensions

Dimensions	3.28 in x 1.41 in x 1.01 in
Display Size	Standard Sized Product
Height	1.01 in

Length	3.28 in
Width	1.41 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L5-15R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 4710CR Specification Sheet French](#)
- [Specifications - 4710CR Specification Sheet English](#)