



Locking Devices, Locking Devices,
Industrial, Flanged Receptacle, 15A 125V, 2-
Pole 3-Wire Grounding, L5-15R, Screw
Terminal, White

By Bryant
Catalog # [4715ER](#)

Locking Devices, Locking Devices, Industrial, Flanged
Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw
Terminal, White

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125V
Phase	Single Phase



Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.50 in
Height	1.68 in
Dimensions	1.84 in x 2.50 in x 1.68 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	15A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786405707

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)