

## Locking Devices, Locking Devices, Industrial, Male Plug, 15A 125V, Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black and White

By Bryant  
Catalog # [4721NP](#)



Locking Devices, Locking Devices, Industrial, Male Plug, 15A 125V, Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black and White

### Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

### Application

Extra Heavy Duty Industrial

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L5-15P

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

### Configuration

Cord Type	All Listed Portables
-----------	----------------------

### Current

Current/Amperage Rating Description	15 Amp
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized
Length	1.53 in
Width	1.53 in
Height	2.18 in
Dimensions	1.53 in x 1.53 in x 2.18 in

### General

Style	Internal Cord Clamp
Color	Black, White
Item Type	15A Triple Gripper Nylon Plug
Material - Mounting Hardware Type	Cord Mounted Plugs
Material	Composite
UPC	781786010000

### Logistics

Carton Quantity	10
Pallet Quantity	4500

### Product Assets

[Catalog \[English\]](#)