



Locking Devices, Locking Devices,
Industrial, Duplex Receptacle, 15A 277V AC,
2-Pole 3-Wire Grounding, L7-15R, Screw
Terminal, Brown

By Bryant
Catalog # 4750DR

Locking Devices, Locking Devices, Industrial, Duplex Receptacle,
15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal,
Brown

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L7-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A



Voltage Rating Description	277V AC
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	277 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	0.93 in
Dimensions	3.28 in x 1.70 in x 0.93 in

General

OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Item Type	15A Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786002128

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)