



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 15A 277V AC,
2-Pole 3-Wire Grounding, L7-15R, Screw
Terminal, Black, With Cover

By Bryant
Catalog # [4761](#)

Locking Devices, Locking Devices, Industrial, Flush Receptacle,
15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal,
Black, With Cover

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	L7-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A



Voltage Rating Description	277V AC
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	277 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Bryant
Style	Box Mounted
Item Type	15A Nylon Single Receptacle- Mounted on 4" Round Metal Box
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786623330

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)