

Locking Devices, Locking Devices, Industrial, Male Plug, 15A 277V AC, 2-Pole3-Wire Grounding, L7-15P, Screw Terminal, Black and White

By Bryant
 Catalog # [4770NP](#)



Locking Devices, Locking Devices, Industrial, Male Plug, 15A 277V AC, 2-Pole3-Wire Grounding, L7-15P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L7-15P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	15 Amp
Description	

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	277 VAC
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	277 VAC

Dimensions

Display Size	Standard Sized
Length	1.53 in
Width	1.53 in
Height	2.18 in
Dimensions	1.53 in x 1.53 in x 2.18 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	15A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786010307

Logistics

Carton Quantity	10
Pallet Quantity	5400

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)