

## Locking Devices, Locking Devices, Industrial, Female Connector Body, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black and White

By Bryant  
Catalog # [4779NC](#)



Locking Devices, Locking Devices, Industrial, Female Connector Body, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black and White

### Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

### Application

Heavy Duty Industrial

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L7-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	277 VAC

Connectivity	Screw Terminals
Voltage Rating	277 VAC

### Dimensions

Display Size	Standard Sized Product
Length	1.53 in
Width	1.53 in
Height	2.95 in
Dimensions	1.53 in x 1.53 in x 2.95 in

### General

Style	Internal Cord Clamp
Color	Black, White
Item Type	15A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Connector Body
Type	Connector Body
Material	Composite
UPC	781786010406

### Logistics

Carton Quantity	10
Pallet Quantity	5400

### Operational

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum Continuous: 75° C</li> <li>• Minimum Continuous: -40° C w/o impact, -25° with impact.</li> </ul>
--------------------	---

### Product Assets

[Catalog \[English\]](#)