



Locking Devices, Locking Devices,
Industrial, Flanged Receptacle, 15A 277V
AC, 2-Pole 3-Wire Grounding, L7-15R,
Screw Terminal, White

By Bryant
Catalog # 4785ER

Locking Devices, Locking Devices, Industrial, Flanged
Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R,
Screw Terminal, White

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L7-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	277V AC



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	277 VAC

Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.50 in
Height	1.68 in
Dimensions	1.84 in x 2.50 in x 1.68 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	15A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786405806

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)