



Locking Devices, Locking Devices,  
Industrial, Flanged Inlet, 15A 277V AC, 2-  
Pole 3-Wire Grounding, L7-15P, Screw  
Terminal, White

By Bryant  
Catalog # 4786MB

Locking Devices, Locking Devices, Industrial, Flanged Inlet, 15A  
277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, White

Features

- Flanged Inlet
- 15A 277V AC
- 2-Pole 3-Wire Grounding
- L7-15P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

|                                       |                                                    |
|---------------------------------------|----------------------------------------------------|
| Environmental Conditions              | Indoor Dry Unless Protected By<br>Additional Means |
| EU RoHS Indicator                     | Yes                                                |
| Standards - RoHS Compliance<br>Status | CM                                                 |
| Nema Rating                           | L7-15P                                             |

Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |
| Number Of Poles | 2-Pole             |

Current

|                            |                             |
|----------------------------|-----------------------------|
| Dielectric Strength        | Withstands 3000V Minimum in |
| Current/Amperage Rating    | 15 Amp                      |
| Description                |                             |
| Current Rating             | 15 A                        |
| Amperage Rating            | 15 A                        |
| Voltage Rating Description | 277V AC                     |
| Connectivity               | Screw Terminals             |



|                |                             |
|----------------|-----------------------------|
| Voltage Rating | 277 VAC                     |
| Dimensions     |                             |
| Display Size   | Standard Sized Product      |
| Length         | 1.84 in                     |
| Width          | 2.50 in                     |
| Height         | 1.68 in                     |
| Dimensions     | 1.84 in x 2.50 in x 1.68 in |

General

|                              |                   |
|------------------------------|-------------------|
| OEM Brand Name               | Hubbell Bryant    |
| Style                        | Equipment Base    |
| Color                        | White             |
| Item Type                    | 15A Flanged Inlet |
| Insulation                   | Insulated Body    |
| Material - Mounting Hardware | Screw Mounting    |
| Type                         | Flanged Inlet     |
| Material                     | Composite         |
| UPC                          | 781786405301      |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Operational

|                    |                                                                                                                             |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Temperature Rating | <ul style="list-style-type: none"><li>• Maximum Continuous: 75° C</li><li>• Minimum Continuous: -40° C w/o impact</li></ul> |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)