



## Industrial Grade, Toggle Switches, General Purpose AC, Momentary Single Pole-Double Throw Center Off, 20A 120/277V AC, Back and Side Wired

By Bryant  
Catalog # 49211

Switches and Lighting Controls, Industrial Grade, Toggle Switches, General Purpose AC, Momentary Single Pole-Double Throw Center Off, 20A 120/277V AC, Back and Side Wired, Ivory



### Features

- Toggle
- General Purpose AC
- Momentary Single Pole-Double Throw Center Off
- 20A 120/277V AC
- Back and Side Wired

### Application

Back and Side Wired

### Current

Current / Amperage Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	120/277 VAC

Voltage Rating 120/277 VAC

### General

Type	Toggle
Series	Extra Heavy Duty
UPC	781786624078
Style	Single Pole Double Throw
Color	Ivory

### Logistics

Carton Quantity 10

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)