



# Industrial Grade, Toggle Switches, General Purpose AC, Double Pole- Double Throw Center Off, 20A120/277V AC, Back and Side Wired

By Bryant  
Catalog # 4925I



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, General Purpose AC, Double Pole- Double Throw  
Center Off, 20A120/277V AC, Back and Side Wired, Ivory

## Features

- Toggle
- General Purpose AC
- Double Pole- Double Throw Center Off
- 20A120/277V AC
- Back and Side Wired

## Application

Back and Side Wired

## General

Catalog Number	4925I
Series	Extra Heavy Duty
Style	Double Pole Double Throw
Type	Toggle

UPC 781786658332

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277 VAC

## Logistics

Carton Quantity 10

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 4925I Specification Sheet English](#)
- [Specifications - 4925I Specification Sheet French](#)