

## Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Hi-Visibility Orange

By Bryant  
Catalog # [5159HVO](#)



Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack, Hi-Visibility Orange

### Features

- Commercial Grade
- Female Connector
- Straight
- 2-Pole 3-Wire Grounding
- 15A 125V

### Application

Heavy Duty

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Current / Amperage Rating	15 A
Connectivity	Screw Terminals
Wattage	1875 W
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb.

### General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Cord Range	0.245"-0.655"
Style	Heavy Duty
Color	Hi-Viz Orange
Item Type	Female Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Thermoplastic
UPC	781786515901

### Logistics

Carton Quantity	10
Pallet Quantity	168

### Operational

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum Continuous: 75° C</li> <li>• Minimum Continuous: -40° C w/o impact, -25° with impact.</li> </ul>
--------------------	---

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)