



Straight Blade Devices, Specialty
Receptacles, Display Case, Receptacle and
Plate, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, Brushed Brass Plate

By Bryant
Catalog # 5236BOX

Straight Blade Devices, Specialty Receptacles, Display Case,
Receptacle and Plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,
Brushed Brass Plate, Single Pack

Features

- Display Case
- Receptacle and Plate
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Commercial/Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V



Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	1.4 lb.

General

Series	Special Use
OEM Brand Name	Hubbell Bryant
Style	Floor Box Assembly
Color	Brass
Item Type	Floor Box Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786424005

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)