



Straight Blade Devices, Short Yoke Receptacles, Panel Mount Single, Commercial/Industrial Grade, Side Wired, Urea Face, 15A 125V, 5-15R

By Bryant
Catalog # 5258



Straight Blade Devices, Short Yoke Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side Wired, Urea Face, 15A 125V, 5-15R, Brown, Single Pack

Features

- Panel Mount Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Side Wired
- Urea Face

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Side Wired Only

Wattage	1875
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	2.25 in
Width	1.38 in
Weight	0.15 lb.
Height	0.85 in
Dimensions	2.25 in x 1.38 in x 0.85 in

General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Brown
Item Type	Panel Mount Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
UPC	781786659209

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)