



Straight Blade Devices, Receptacles, Single, Corrosion Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack

By Bryant
Catalog # 5261CR



Straight Blade Devices, Receptacles, Single, Corrosion Resistant,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15R, Yellow, Single Pack

Features

- Single
- Corrosion Resistant
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 125V

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5261CR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786659308

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.15 lb

Width 1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 5261CR Specification Sheet English](#)
- [Specifications - 5261CR Specification Sheet French](#)