



## Straight Blade Devices, Receptacles, Single, Weather Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown

By Bryant  
Catalog # [5261WR](#)

Straight Blade Devices, Receptacles, Single, Weather Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

### Features

- Single
- Weather Resistant
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 125V

### Application

Extra Heavy Duty Industrial Specification Grade

### Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired



Wattage	1875
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Weight	0.15 lb.
Height	0.91 in
Dimensions	3.28 in x 1.38 in x 0.91 in

### General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Brown
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
UPC	781786670655

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)