



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red

By Bryant
Catalog # 5262BRED

Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red

Features

- Slender/compact design
- Finder Groove Face
- Triple wipe contacts

Application

Hubbell-Pro Extra Heavy Duty

Specifications

Environmental Conditions	Indoor Dry unless protected by additional means
Nema Rating	5-15R
Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant


Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875 W
Connectivity	Back and Side Wired
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions



Length	3.28 in
Display Size	Standard Sized Product
Weight	0.25 lb.
Height	0.92 in
Width	1.38 in
Size	Standard Sized Product
Dimensions	3.28 in x 1.38 in x 0.92 in

General

Color	Red
Style	Finder Groove Face
Series	Hubbell-PRO
OEM Brand Name	Hubbell Bryant
Mounting Type	Screw Mount
UPC	781786715073
Type	Standard Duplex
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex
Material	Thermoplastic/Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum continuous 75°C • minimum -40°C (w/o impact)
--------------------	--

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)