



Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red

By Bryant
Catalog # 5262BREDWR

Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red



Features

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- Triple wipe contacts
- Compact design

Application

Hubbell-Pro Extra Heavy Duty

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired

Wattage	1875 W
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Size	Standard Sized Product

General

Series	Hubbell-PRO
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Red
Item Type	Duplex
Material - Mounting Hardware	Screw Mounting
Type	Weather Resistant Duplex
Material	Thermoplastic/Composite
UPC	781786670051
Mounting Type	Screw Mount

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum continuous 75°C • minimum -40°C (w/o impact)
--------------------	--

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)