



Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, White

By Bryant  
Catalog # 5262BWWR

Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, White

Features

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- Triple wipe contacts
- Compact design

Application

Hubbell-Pro Extra Heavy Duty

Specifications

|                          |                                                                                                     |
|--------------------------|-----------------------------------------------------------------------------------------------------|
| Environmental Conditions | Weather Resistant                                                                                   |
| EU RoHS Indicator        | No                                                                                                  |
| Industry Standard(s)     | UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant |
| Nema Rating              | 5-15R                                                                                               |

Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |
| Number Of Poles | 2-Pole             |

Current

|                           |                     |
|---------------------------|---------------------|
| Current Rating            | 15 A                |
| Amperage Rating           | 15 A                |
| Phase                     | Single Phase        |
| Current / Amperage Rating | 15 A                |
| Connectivity              | Back and Side Wired |



|                |        |
|----------------|--------|
| Wattage        | 1875 W |
| Voltage Rating | 125 V  |

Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Size         | Standard Sized Product |

General

|                              |                          |
|------------------------------|--------------------------|
| Series                       | Hubbell-PRO              |
| OEM Brand Name               | Hubbell Bryant           |
| Style                        | Finder Groove Face       |
| Color                        | White                    |
| Item Type                    | Duplex                   |
| Material - Mounting Hardware | Screw Mounting           |
| Type                         | Weather Resistant Duplex |
| Material                     | Thermoplastic/Composite  |
| UPC                          | 781786670013             |
| Mounting Type                | Screw Mount              |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Operational

|                    |                                                                                                                |
|--------------------|----------------------------------------------------------------------------------------------------------------|
| Temperature Rating | <ul style="list-style-type: none"><li>• Maximum continuous 75°C</li><li>• minimum -40°C (w/o impact)</li></ul> |
|--------------------|----------------------------------------------------------------------------------------------------------------|

Product Assets

- [Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[French, English\]](#)