



Straight Blade Devices, Equipment Base
Devices - Clamp Type, Back Wiring, Female
Nylon Cup, Industrial/Commercial, 15A
125V, 5-15P

By Bryant
Catalog # [5279](#)

Straight Blade Devices, Equipment Base Devices - Clamp Type,
Back Wiring, Female Nylon Cup, Industrial/Commercial, 15A 125V,
2-Pole 3-Wire Grounding, 5-15P, White, Single Pack

Features

- Back Wiring
- Female Nylon Cup
- Industrial/Commercial
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Commercial/Industrial

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A



Voltage Rating	125 V
Wattage	2500
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Length	1.84 in
Display Size	Standard Sized Product
Weight	0.1 lb.
Height	1.31 in
Width	2.50 in
Dimensions	1.84 in x 2.50 in x 1.31 in

General

Color	White
Style	Clamp Type
Series	Heavy Duty
UPC	781786659957
Type	Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Flanged Single

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)