



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled 12 Position, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, SinglePack

By Bryant
Catalog # 5295

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled 12 Position, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, White, SinglePack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Angled 12 Position
- 2-Pole 3-Wire Grounding
- 15A 125V

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-15P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Portable
-----------	--------------

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V



Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Screw Terminals
Wattage	1875
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized
Length	1.25 in
Width	2.07 in
Weight	0.2 lb.

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Cord Range	0.300"-0.655"
Style	Extra Heavy Duty
Color	Black
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Nylon
UPC	781786174108

Logistics

Carton Quantity	10
Pallet Quantity	4800

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)