



## Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, Red, Single Pack

By Bryant  
Catalog # [5342RED](#)



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, Red, Single Pack

### Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Side Wired
- 20A 125V

### Application

Extra Heavy Duty Compact Industrial Specification Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A

Connectivity	Side Wired Only
Wattage	2500
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Weight	0.2 lb.
Height	0.92 in
Dimensions	3.28 in x 1.38 in x 0.92 in

### General

Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Red
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
UPC	781786714694

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)