



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, Side Wired, 20A 125V, 5-20R, White, Single Pack



By Bryant  
Catalog # [5342W](#)

Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Side  
Wired, 20A 125V, 5-20R, White, Single Pack

## Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Side Wired
- 20A 125V

## Application

Extra Heavy Duty Compact Industrial Specification Grade

## General

Catalog Number	5342W
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786714779

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	3.28 in

Weight	0.25 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 5342W Specification Sheet French](#)  
[Specifications - 5342W Specification Sheet English](#)