



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Black, Single Pack

By Bryant
Catalog # [5361BLK](#)

Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Black, Single Pack

Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 125V
- 5-20R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

| | |
|--------------------------|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | Yes |
| Nema Rating | 5-20R |

Conductor

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole |

Current

| | |
|----------------------------|---------------------|
| Current Rating | 20 A |
| Amperage Rating | 20 A |
| Voltage Rating Description | 125 V |
| Phase | Single Phase |
| Current / Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |



| | |
|----------------|-------|
| Wattage | 2500 |
| Voltage Rating | 125 V |

Dimensions

| | |
|--------------|-----------------------------|
| Display Size | Standard Sized Product |
| Length | 3.28 in |
| Width | 1.38 in |
| Weight | 0.15 lb. |
| Height | 0.91 in |
| Dimensions | 3.28 in x 1.38 in x 0.91 in |

General

| | |
|------------------------------|--------------------|
| Series | Extra Heavy Duty |
| OEM Brand Name | Hubbell Bryant |
| Style | Finder Groove Face |
| Color | Black |
| Item Type | Single |
| Material - Mounting Hardware | Screw Mounting |
| Type | Single Receptacle |
| UPC | 781786714724 |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)