



Straight Blade Devices, Receptacles, Single, Corrosion Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Single Pack

By Bryant
Catalog # 5361CR

Straight Blade Devices, Receptacles, Single, Corrosion Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Yellow, Single Pack

Features

- Single
- Corrosion Resistant
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 125V

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase



Current / Amperage Rating	20 A
Connectivity	Back and Side Wired
Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Weight	0.15 lb.
Height	0.91 in
Dimensions	3.28 in x 1.38 in x 0.91 in

General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Yellow
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
UPC	781786660700

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)