



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, Isolated Ground, Weather Resistant, 20A 125V, 5- 20R

By Bryant
Catalog # 5361IGWR



Straight Blade Devices, Receptacles, Single,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Isolated
Ground, Weather Resistant, 20A 125V, 5- 20R, Orange, Single
Pack

Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Isolated Ground
- Weather Resistant

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5361IGWR
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786670464

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in

Weight	0.1 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 5361IGWR Specification Sheet French](#)
- [Specifications - 5361IGWR Specification Sheet English](#)

