



# Straight Blade Devices, Female Connector Body, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Black, Single Pack

By Bryant  
Catalog # 5369B



Straight Blade Devices, Female Connector Body, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Black, Single Pack

## Features

- Valise Series
- Commercial Grade
- Straight
- 2-Pole 3-Wire Grounding
- 20A 125V

## Application

Heavy Duty

## General

Catalog Number	5369B
Cord Range	0.245"-0.655"
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786731271

## Dimensions

Display Size	Standard Sized Product
Height	1.38 in
Length	2.68 in
Weight	0.15 lb

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 5369B Specification Sheet English](#)
- [Specifications - 5369B Specification Sheet French](#)