



Straight Blade Devices, Male Inlets,
Flanged, Industrial/Commercial, Self-
Grounding Strap, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20P, Single Pack

By Bryant
Catalog # 5378G

Straight Blade Devices, Male Inlets, Flanged,
Industrial/Commercial, Self-Grounding Strap, 20A 125V, 2-Pole 3-
Wire Grounding, 5-20P, Black, Single Pack

Features

- Flanged
- Industrial/Commercial
- Self-Grounding Strap
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20P

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Current / Amperage Rating	20 A
Connectivity	Screw Terminals
Wattage	2500
Voltage Rating	125 V



Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.50 in
Weight	0.1 lb.
Height	1.55 in
Dimensions	1.84 in x 2.50 in x 1.55 in

General

Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Clamp Type
Color	Black
Item Type	Single Flanged
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
UPC	781786661318

Logistics

Carton Quantity	100
-----------------	-----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)