



Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

By Bryant
Catalog # [5379](#)

Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, Nylon Cup, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

Features

- Flanged
- Industrial Grade
- Nylon Cup
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Commercial/Industrial

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V



Wattage	2500
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	1.84 in
Display Size	Standard Sized Product
Weight	0.05 lb.
Height	1.31 in
Width	2.50 in
Dimensions	1.84 in x 2.50 in x 1.31 in

General

Color	White
Style	Clamp Type
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
UPC	781786661356
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Item Type	Flanged Single

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)