



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, White, Single Pack

By Bryant
Catalog # [5478](#)

Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, White, Single Pack

Features

- Flanged
- Industrial/Commercial
- Nylon Cup
- 20A 250V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	6-20P

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	250 V
Dielectric Strength	Withstands 3000V Minimum in
Current Rating	20 A
Voltage Rating	250 V
Wattage	5000
Connectivity	Screw Terminals
Current / Amperage Rating	20 A



Dimensions

Length	1.84 in
Display Size	Standard Sized Product
Weight	0.05 lb.
Height	1.55 in
Width	2.50 in
Dimensions	1.84 in x 2.50 in x 1.55 in

General

Color	White
Style	Clamp Type
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
UPC	781786662902
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Insulation	Insulated Body
Item Type	Single Flanged

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)